



APPARATUS PROPOSAL

Date: 12/30/19

This Proposal has been prepared for:
Chief Rob Angell
Pinellas Park Fire Department

Hall-Mark RTC is pleased to offer the Pinellas Park Fire Department (1) Wheeled Coach 2021 Freightliner M2 rescue. **Pricing is based on the Florida Sheriff's Association Contract FSA18-VEF13.0, Specification #3, 170" x 95" x 72".** This vehicle shall be in accordance with the attached specifications. The purchase price shall also include all vehicle components and NFPA equipment as requested and listed in the attached documentation. Delivery will be F.O.B. to Pinellas Park and will be made approximately 120-150 days after receipt of the chassis. This Quote is valid for 60 days unless extended in writing.

FSA 18-VEF13.0 Specification #3	\$	186,190
Options added by	\$	42,959
Customer Discount	\$	-6,000
Sub Total	\$	223,149
Total Price for 1 Rescue	\$	223,149

Rick Schoppe - Account Manager
725 SW 46th AVE, Ocala, FL 34474 (407) 907-2444

12/30/19

Date

Dee Daniels - Director of Sales
725 SW 46th AVE, Ocala, FL 34474 (352) 629-6305

12-30-19

Date

QUOTATION

REV, RTC

Pinellas Park
Rob Angell
11350 43rd Street
Pinellas Park, FL
727-369-5810

Wheeled Coach Industries, Inc.
Rick Schoppe
1 Unit
SHA,

Exp. Date: 01/20/2020

Quote No: PIN001-

12/30/2019 10:52:31

WO#:

Page 1

PART NO	S	DESCRIPTION	QTY
== Freightliner, (SO) 170" Module, Custom - 620.033 08/05/16 ==			1
00-00-0247		***** OUTSIDE GRAPHICS- 24/7 *****	1
	<	CHASSIS:	1
		Some ref pics on server Customer's last unit for ref only 369078, new unit has changes.	
00-90-2028	S < >	2021 Freightliner, M2, 260HP, EVS 2200 WC Std. spec (SO)	1
		SR - #2181977R-1	
		Chassis spec on server in work order folder.	
		FUEL TANK(s) mounted between rails aft of rear axle	
		Hood mounted OEM air horns with OEM foot switches.	
		Unit will be painted Overall Red FLNA 30012, see paint option.	
		Spare Tire, None	
CAB TO MODULE MOUNTING:			1
10-10-8000	< >	Bellows, Passthru, Unigrip, Freightliner, Std	1
		with aluminum cab insert.	
BASE BILL OF MATERIALS			1
15-11-9376	<	2019, Base, Freightliner, 170" Module, Standard Model 2019-1	1
		Reference only 369078	
CHASSIS ADD-ONS:			1
1A-10-0100	S < >	Lettering/Graphics, By Outside Vendor	1
		SR - #2181977F	
		Location:24/Seven	
		# of Days:2	
		**Includes Front bumper and rear DG chevrons.	
1A-10-0101	XU <	Four (4) #520-0676-00 headset hangers	4
		SR-2181977F)	
		Add "2" sturdy hooks to replace OEM hooks. Also, add "2" sturdy hooks to front headliner area. Customer to hang headsets and radios. "Please see salesman for exact placement" Black hooks from Firecom - Part #520-0676-00	

PART NO	S	DESCRIPTION	QTY
SUSPENSION:			1
1F-31-0000	< >	Switch, (2), Momentary, Dump (1) - just inside right rear entry door, on RR cabt, down low, with Elec lock switch (Recessed) (1) - In cab console	1
1F-31-3000	<	Air Suspension, OEM, Installed, FrtlNr W/(2) OEM leveling valves. Only to dump in neutral when park brake is set. OEM air gauge in dash.	1
ALTERNATOR(S):			1
1K-40-5000	< >	Alternator,OEM Per chassis spec on server in wo folder	1
THROTTLE CONTROLS:			1
1P-50-5000	<	High Idle Controls, OEM Switch in Dash, Freightliner w/label above both switches.	1
CAB STEP:			1
20-60-1050	S <	Cover, Diamond Plate, w/(2) Steps, M2 Per Eng design reference 369078	1
20-60-1051	XU <	Cover, Def Tank, Diamond Plate SR2181977F (SAP# 10360842)	1
20-60-5150	<	Steps, Cab, Gatorgrip, FrtlNr M2, C/S Per Eng design reference 369078	1
CHASSIS ADD ONS, MISC			1
2F-71-4000	< >	Ignition Security System, ETI-ISSO-P/ETISSO-07+(Not Dodge) with switch located on dash to the right of the steering column Will need Elec Eng review? Ref 319016-18 or 369078	1
HEATING/AIR CONDITIONING:			1
5U-12-5000	>	Hoses, Heater, No Max, to Rear, STD	1
5U-70-0823	< >	Heat/AC, FrtlNr, Combo, w/Coolbar, DAK Ducted **Please make sure one duct is directly over the attendant seat. with thermostat in action area. 12vdc External Condenser, in Coolbar mounted on front of module. Painted. RED FLNA 30012	1
BATTERY SWITCHES:			1
60-22-1070	<	Battery Sw, 5min Timer, FrtlNr M2/F-650, Fig 5B Activated thru OEM ignition switch timer function upon ignition "off". Momentary rocker switch, on driver's side of cab console, to function as timer shutoff and also reactivate timer.	1

PART NO	S	DESCRIPTION	QTY
		ONLY Module power is turned on/off. Chassis power is NOT turned off.	
		BATTERY TRAY:	1
60-40-3020	< >	Tray,(4) batt, Slide-Out, (2)Gator Grip Step, FrtlNr, 2012+	1
		w/turtle-tile installed at bottom of tray. (3) OEM batteries. Under driver's side cab door. Ref 369078.	
		CONSOLES:	1
7U-10-01SR	XU <	Storage pocket installed on the lower portion of the OEM cab (SO-SPKT-369078) SR# -2181977F	1
		Fabricated aluminum storage pockets installed on the lower portion of the OEM cab doors. (See photo's in file) Ref 369078	
7U-10-7000		Console, A/A, Wood, Angled	1
7U-12-00SR	XU <	Custom Console - Aluminum with black coating (SAP # 1036085)SR2181977F	1
		Pending customer design - Black scorpion finish	
		complete flat console with separate black panel for radio install. See Dealer for drawing.	
		Note add Pinked work order	
		SIREN SPEAKERS:	1
DF-10-7400	<	Speakers, (2), Cast, #SA5403-M2-1, FrtlNr M2, Std installed in bumper.	1
		== Type 9 - 170" Module, Custom Series - 620.033 08/05/16 ==	1
35-05-0300		Type 9 - 170" Module - Custom Series	1
35-05-0310		Type 9 - 170" Module General Body Construction Spec	1
35-05-0320		Type 9 - 170" Module Vehicle Body Structure Spec	1
35-05-2000		INTERIOR CABINETS -Duralite Construction, Wood, CN10 compliant	1
	<	MODULE BODIES:	1
		Lighting, Compt, LED Hi-Brite Flex, ILOS 6" drop skirt ILOS	
35-10-0064	<	Aisle Space, per KKK, STD	1
		Install anti-slip decal with Wheeled Coach logo on curbside and rear stainless steel thresholds, STD	
35-10-0962	>	Headroom, 72" H.R. Type 9 - 170" module Standard Model	1
35-11-0300	< >	Drop Skirt, 6 inches forward of rear wheels, Both sides Note: Bright finish fender flares will not work, must use rubber	1
37-00-0350	<	Coating, Polyurethane, Per compartment (1) Each light gray	5
37-00-0360		Coating, Polyurethane, Rear Bumper Supports	1
37-00-0710	<	Duraseam Doors, with Hidden Jambs - Magnetic door switches, Standard	1
37-00-0900	< >	Compartments, Std, Floor 3" Drop Down from Door Opening, MAV compts A, B, D,& E are STD drop down floor	4

PART NO	S	DESCRIPTION	QTY
37-00-1000	< >	Compartments, Sweepout , MAV	1
		compt "F" std sweep out, 13" from wall #3	
		FUEL FILL HOUSING:	1
3A-10-1000	>	Housing, Fuel Fill, Cast, F1/C1/D1/M2	1
3C-00-0000	< >	Type 9 - 170" Module, EMS With 0.125 module skins, std.	1
3D-A0-0300	< >	A, Compt, Std, Hoseline, 170" Module, T9, Fire Rescue, 72" H Please see dealer for installation of fixed divider.	1
		Single Door. Ref 369078 this unit has 6" drop skirt. FW Scoop stretcher storage in forward portion of compt. 3 Navaho back board storage, just rearward of scoop stretcher. C/S Entry door moves rearward to rear wheel well.	
		Eng note see (Vent, Clamshell, Exterior ,IATS)	
3D-B1-0450	<	B1, Compt, Widened and Raised, 170" Module, T9, 72" H.R Raised to the top of the squad bench. Single Door. Ref 369078	1
3D-B2-0200		B2, Compt, Deleted, 170" Module, T9, 72" H.R.	1
3D-D0-06SR	XS < >	D, Compt, Custom, 170" Module, T9 (SO-D-369078) SR #2181977F Engineering note install exhaust vent on top of RR cabinet, per Eng design Full Height, single door	1
		Eng note see (Vent, Clamshell, Exterior, IATS)	
3D-E0-0100	<	E, Compt, Std, 170" Module, T9 Single Door	1
3D-F0-03SR	XS < >	F, Compt, Custom, 170" Module, T9 (SO-F-369078) SR #2181977F Per Eng Design	1
		Single door, Custom width 5" wider than normal	
		Eng note O2 flap ILOS	
		EXTERIOR DIVIDERS:	1
3F-10-5500	<	Divider, Vertical, Custom, (1), Mounted: 3/16" mill finish aluminum located in right front compt "A" for backboards and scoop.	1
		Cmpt "A" divider to split the compartment in half. Add note for seatbelt to attach from middle of wall 2 to front edge of wall 3 on the forward side of the divider for backboards.	
		SHELF- COMPARTMENT "A"/RF CABINET:	1
3F-20-1000	< >	Shelf, Adjustable,(1), RF Cabt Custom 3/16" mill finish aluminum (1) RF compt "A"/cabt (3 shelves evenly spaced)	1

PART NO	S	DESCRIPTION	QTY
3F-20-1500	< >	Shelf, Additional, Adjustable, (1), RF Cab Custom 3/16" mill finish aluminum (2) RF compt "A"/cabt for a total of 3 shelves	2
SHELF- COMPARTMENT "D":			1
3F-40-3001	< >	Shelf, Custom, Adj, Cmpt "D", (1), Std Model only 3/16" mill finish aluminum Compt "D" at inside/outside opening	1
3F-40-3500	<	Shelf, Custom, Adj, Cmpt "D", (1), Addt'l 3/16" mill finish aluminum (2) Compt "D" above and below the other shelf at ISOS opening	2
SHELF- COMPARTMENT "E":			1
3F-50-0100	<	Shelf, Fixed, Cmpt E, for Electrical storage, w/ Divider Eng: set up to be used with a poured tray	1
COMPARTMENT / SHELF, MISC:			1
3F-70-10SR	XU <	Heavy Duty Shelf Brackets 1/4" Aluminum ILOS (SO-BRACK-369078) SR# - 2181977F	1
WINDOWS:			1
3P-10-5201	>	Window,Upper,CS/Slider,Rr/Fixed,Priv Tint,PAN,Std Model only	1
MODULE ENTRY DOOR HANDLES:			1
3U-30-8010		Handles, Patient Entry, Trimark, Chrome "SafePass" ILOS	1
EXTERIOR COMPT DOOR HANDLES:			1
3U-40-0512	>	Handle, Module Compt, Trimark, Chrome, ILOS	5
3U-60-0100	>	ELECTRIC DOOR LOCK PACKAGE OPTIONS: Click to add	1
3U-60-0101	XU <	Switch, Stealth, Cab/Body Doors, with Red Cover ILOS (SO-SW-351192) #SR 216814F with red cover streetside rear of truck underneath an inlet cover, mounted to house the stealth switch under the auto eject red cover. Next to shore line inlet.	1
3U-60-1390	< >	Door Locks,Electric, Trimark, (1)DOOR, Entry Door Module entry doors.	2
3U-60-1400	< >	Door Locks,Electric, Trimark, (1)DOOR, Compt Door All module compts	5
3U-60-1500	< >	Switch,Momentary Rocker,Activate Elect Door Locks (1) - Installed on C/S wall at head of S/B. (1) - Installed just inside RR entry door, on CSR cabt, down low, with Dump switched (Recessed)	2
3U-60-2950	< >	Relay Control Circuit,Elect Locks,w/(2)Keyless Entry Fobs #PLRB-RC	1
3U-60-5200		Circuit, OEM Door Lock to activate Mod Doors(not Dodge)	1

PART NO	S	DESCRIPTION	QTY
DOOR HOLD OPENS:			1
40-10-1050	< >	Hold Open, Cast, Grabber (1), 3 in., ILOS	2
		LOCATION: Top and bottom of compt "A" door	
40-10-1611	< >	Hold Opens,Rr Doors,Cast,Grabber (2), 5.5", Std Model only -Installed so doors will open as wide as possible -Mount at BOTTOM of doors	1
		Eng note: See tail lights and SL inlet ILOS	
40-10-7100	< >	Holdopen, Gas Strut, Ext Compt, 60lb , Std	2
		Compartments "D" and "F"	
40-10-7200	<	Hold Open, Gas Strut, Ext Compt, 30lb, Std Compartments "B" and "E"	2
40-10-7750	<	Holdopen, Gas Strut, CS Entry Door, 35# Standard. New Code Per ECN 1823	1
DOOR PANELS:			1
45-10-0001	XU <	Panels, Entry, Durasafe, Stainless Steel, w/Chevrons, ILOS (SO-PNL-369078) 45-10-4505 -Durasafe design -aluminum center panels covered: red/yellow reflective tape. To match rear chevron color	1
FENDER FLARES:			1
4A-10-1001		Flare, Fender, Rear, Black Rubber, Std Model only	1
BUMPERS:			1
4F-11-3000		Dock Bumpers, Black, On Rear, Mods	1
4F-12-0002	< >	Bumper,Rear,Frtlnr/Int'l,Std,W/Skids & w/LED DOT lights, St	1
		w/ Gator Grip on flip up step. Reinforced, std on MAV	
SKIRTRAILS			1
4U-10-9210		Skirtrails,Extruded Rubber w/Refl Tape,170-175" Module	1
4U-10-9500		Tape, Reflective, White, For Extruded Skirtrails	1
STONE GUARDS (FRONT):			1
4U-11-6000	<	Stone Guard, Front, Dia Plate, 24"	1
		fill top of stone guard with clear silicone.	
KICKPLATES (w/STD. REAR STONEGUARDS):			1
50-10-0001	XU <	Kickplate, Mav, w/Recess Custom, Duraseam (SO-KP-369078) Per Eng design with 1 - 7 series warning light on each end *Kickplate will need notches cut out above the frame rail. Previous units all damaged. Please see photos and contact Rick Schoppe with questions.	1
MODULE ADD-ONS:			1
55-10-0001	XU <	Front license plate sign/blank plate (SO-SIGN2-369078) Aluminum plate to fit in front license plate holder ref - 369078	1

PART NO	S	DESCRIPTION	QTY
		Install in front license plate holder	
55-10-0002	XU <	Sign Holder Special (1) ILOS (SO-SIGN1-369078) SR# - 2181977F	3
		3 - 3 sided number sign holders and 3 placards. Please reference 369078 for sizes. All holders and placards painted to match box.	
55-10-1000	< >	Vent, Clamshell, Exterior, IATS	2
		location: Compt "A" and "D". Same as 369078	
55-10-3000	<	Holder, License Plate, Cast, C30002, STD - in rear kick plate, centered	1
		SILL PROTECTORS	1
55-30-4001		Sill Protectors, Stainless, All Compts, Std Model only	1
		MODULE STEPWELL:	1
55-90-6030		Stepwell, Double Step, ILOS, MAV	1
		MUD FLAPS:	1
5A-10-1001		Mud Flaps, Rear, W/Logo, Std Model only	1
	<	PAINT/BELTS:	1
		Paint shop - paint ship loose sign holder frames Red FLNA 30012 to match the unit. "3" in total.	
		Unit gets a rear chevron	
5F-10-3700	< >	Paint, Entire Units, MAV Units, Red &/or Metallic Sikkens paint code #__FLNA30012 Red	1
		Module roof Painted White: CHA88:GW6 inside the roof rails/welds	
		You will not see white roof paint when standing on the ground next to the unit.	
		DECAL PACKAGES INSTALLED:	1
5P-10-5001		Roof Star, White Border, Installed, Std Model Only	1
		ELECTRICAL SYSTEM: Circuitboard	1
		COAX CABLES/ANTENNAS:	1
65-30-1000	< >	Coax Cable, RG58/U, (1) Each, Standard, Terminate: Module roof port #4 to behind passenger seat with 6' pigtails	1
65-30-6500	< >	Base- Antenna, Motorola Mount, W/Coax	3
		(3) - (1) Port 1, (1) Port 2, (1) Port 3	
		terminate in center console, with a six foot tail	
		12VDC POWER SOURCES & OUTLETS:	1
6A-22-200E	< >	Outlet, Cigar Lighter, STD, (2), A/A - on standard 20-amp ignition hot circuit. ("elect batt sw")	1
6A-22-2500	< >	Outlet, Cigar Lighter, IATS, (1) Constant hot (1) in the RF cabt, wall #1, near wall 2, up high will require a build up, due to compt style. (1) Pass side/side of CC, forward of MDT reinforced area	2

PART NO	S	DESCRIPTION	QTY
6A-22-5100	<	Outlet, Dual USB Port, 5VDC, 2.1Amp output, Standard (1) Located on the passenger side of the center console, per Electrical Engineering - CONSTANT HOT (1) Located on the driver side of the center console. - CONSTANT HOT	4
POWER SOURCE, 12 VDC			1
6A-23-0910	<	Power Source, 12VDC, 20A, Ignition/Shoreline Hot (1) pre-wire coil and tagged in action area (1) pre-wire coil and tagged behind driver's seat.	1
6A-23-3800	< >	Power Source, 12 VDC, 40 Amp (+-) Powered by: Constant Hot Terminate in cab console, attached to buss bar	1
6A-24-1100	< >	Buss Bar Assembly (+/-), 5 Position, for ground and hot - cab console, see 40 amp pwr source.	1
ELECTRICAL ACCESSORIES			1
6E-10-4456	<	Camera, Backup, Safety Vision, SV 630V camera w/ 4.3" mirror Monitor Mount camera exterior on rear of module, off center toward driver's side.(if there's a center light) Mount monitor in place of the OEM mirror	1
SHORELINE INLETS:			1
6F-80-5400	< >	Shoreline Indicator Light, 125 VAC, LED, Green above shoreline inlet	1
6F-90-4107	< >	Super Auto Eject, 20 amp, ILOS, Yellow, Std Model Only 20 amp auto eject S/L, mounted on rear of unit driver's side above kick plate see CA drawings on server.	1
125 VAC OUTLETS:			1
6K-40-1000	<	Outlet, 125 VAC, Duplex, (2), STD - (1) outlet in action area - (1) telemetry area, wall #2, down low and centered	1
6K-40-2000	< >	Outlet, 125 VAC, Duplex, IATS (1) - passenger side of console (1) - Compt "D" wall 3, mid-height in access panel . Install the 110V outlet between adjustable middle shelf and top adjustable shelf on wall #3 of cmpt "D"	2
INVERTERS:			1
7F-10-9000	< >	Inverter/Charger, Vanner 20-1050CUL-DC - Mounted on ceiling in Compartment "E"	1
PREWIRES:			1
7P-40-5000	< >	Prewire, Opticom, In Drive Gear Set up per Elec Eng. Ref 369078 SR# - 216930F Switch in cab console, terminate wiring in the Cool Bar middle lower area, with a 6 ft tail, tagged as needed.	1
GAUGES/METERS:			1

PART NO	S	DESCRIPTION	QTY
D0-10-6500	<	Alarm, Low Voltage, Audio/Visual Light in cab console and Buzzer in cab.	1
DA-10-4000		Switch, Emergency Master, Non Seq	1
		SIRENS:	1
DK-10-1400	>	Siren, Whelen, WS-295-SLSA1, Standard	1
	<	AIR HORNS:	1
		OEM air horns one each side of hood and foot switches one each side driver and passenger side provided on OEM chassis.	
		SWITCHING OPTIONS FOR AIR HORNS & SIRENS:	1
DP-11-1000		Switch, Siren/Horn Thru Horn Ring	1
		AUDIBLE ALARMS:	1
F0-11-1500		Alarm, Back-up, No Cutoff Switch	1
		VEHICLE EXTERIOR LIGHTING	1
FF-10-6000	< >	Cab Headliner Removal Fee, MAV for lightbar installation	1
		WHELEN M9 SERIES LED FLASHING LIGHTS:	1
FU-41-0105	< >	Light, M9RC, LED, Whelen, Red, Clear Lense, ILOS, W/Flange (2) - each side standard location (2) - on front in upper outer corners (2) - on rear in upper outer corners	8
		Prim/Secon through lights internal flasher - Action flash	
FU-41-0107	< >	Light, M9RC, LED, Whelen, Red, Clear Lense, IATS, W/Flange (2) - on either side of clear on CoolBar (2) - Rear of module to show through rear windows	4
		Prim/Secon through lights internal flasher - Action flash	
FU-41-0110	< >	Light, M9AC, LED, Whelen, Amber, Clear Lense, ILOS, W/Flange centered over rear doors	1
		Prim/Secon through lights internal flasher - Action flash	
FU-41-0114	< >	Light, M9C, LED, Whelen, Clear, ILOS, W/Flange Center of CoolBar	1
		Prim only wired through internal flasher - Action Flash	
FU-41-0130	< >	Light, M9D, LED, Whelen, R/C, Clear Lense, ILOS, W/Flange On angled portion of CoolBar	2
		Prim/Secon wired through internal flasher - Action flash	
		WHELEN M7 SERIES LED FLASHING LIGHTS:	1
H5-58-0620	< >	Light, M7RC, LED, Whelen, Red, Clear Lens, ILOS Grille lights ILOS	2
		Prim only wired through internal flasher - Action Flash	
H5-58-0625	< >	Light, M7RC, LED, Whelen, Red, Clear Lens, IATS (2) rear intersection, over rear wheel well Prim only through lights internal flasher - Action Flash	4

PART NO	S	DESCRIPTION	QTY
		(2) In rear kickplate, one each side	
		Prim/Secon through lights internal flasher - Action Flash	
		WHELEN FLANGES 7 SERIES LIGHTS	1
H5-59-1020	<	Flange, Whelen, Chrome, M7FC, each	6
		For M7 Series Lights	
		WHELEN M4 SERIES LED FLASHING LIGHTS:	1
H5-59-3130	<	Light, Whelen, M4D Red/ Clear, Lens clear, ILOS Front intersection lights	2
		Prim only through lights internal flasher - Action Flash	
		NOTE: FRONT INTERSECTION LIGHTS TO BE AS FAR FORWARD AS POSSIBLE FORWARD OF AIR HORNS	
H5-59-3135	<	Light, Whelen, M4D Red/ Clear, Lens clear, IATS IATS intersection lights, mounted on hood just rearward of airhorns	2
		Prim only through lights internal flasher - Action Flash	
		CORNER CAP LIGHTS	1
HF-11-6049	<	Corner Cap Lts,Multi-LED,(2)Amber(2)Red w/Flashers,Std Model - High intensity flashers; thru separate switch	1
		CLEARANCE LIGHTS:	1
HF-12-9100	<	Light, Clearance, Amber LED, ILOS - On front as clearance lights.	3
HF-12-9601	<	Light, Clearance, Red LED, Std Model only - On rear as clearance lights.	3
		SCENE AND LOAD LIGHTS	1
HK-20-130N	<	Light, LED, Whelen, Clear, #M9LZC w/Flange, ILOS, (1) (1)#AS00344, (1)#AS89004	6
		(2) on rear as load lights	
		(4) as scene lights	
J0-42-7100	>	Circuit, Neutral Power, C1/C3/F1/F3/D1, 2001+	1
		HARNES LAYOUT:	1
J5-13-4000		Mod Ty 1 Whelen "E" Spec, No LB	1
		STOP/TURN/TAIL LIGHTS:	1
JA-10-1200		Light, License Tag, (2), Trucklite #15205 LED, ILOS	1
JA-13-8010	<	Tailights, Whelen,LED Stop/Tail,Halogen/Backup, w/ WC logo - Brake- Alert Flash before the steady Burn - Turn Arrow – sequential arrow	1
		Eng note - move up for SL inlet and SL ind light	
		MODULE OVERHEAD HEADLINER:	1
JK-10-5510	<	Headliner, Flat, Expanded PVC, 160"+ MAV/Type 1	1

PART NO	S	DESCRIPTION	QTY
		Eng note see HVAC option (**Please make sure one duct is directly over the attendant seat.)	
		12VDC INTERIOR LIGHTING:	1
JP-10-0512		> Lights, Dome, LED, Weldon #8049-0000-3W, (4) S/S, (3) C/S	1
JP-10-0522		< > Light, Dome, LED, Weldon #8049-0000-3W, IATS Position 9 over step well switch with CS dome lights	1
JP-10-7015		Light, Stepwell, LED, Whelen #TOCACCCR, 2in, ILOS	1
JP-10-80SR	XU <	LED counter top lights (SO-LT1-369078) SR# -2181977F Switch in AA sw panel for light LED action area light Whelen #0AC0EDCR (1) mounted under cabt "L" for streetside AA (1) mounted under cabt "K" for rear telemetry	2
		SWITCHING OPTIONS FOR 12VDC INTERIOR LIGHTI	1
JP-11-7500	< >	Switch, 12 VDC, (1), For Additional Lights (1) AA switch panel for LED AA light (1) AA switch panel for LED Telem light	2
		LIGHTS & MISCELLANEOUS:	1
JR-50-2880	<	Lighting, Compt, LED Hi-Brite Flex, ILOS both vertical edges near door jambs, compts "A", "B1", "D", "E", & "F". Retain 2" O2 light.	1
JR-60-2003	< >	Timer, Momentary Sw, 15 Minute, Constant Hot, Std Model only Mount switch on C/S wall at the head of the squad bench in the standard location. Switch to allow activation and also deactivation. Wire to street side domes on high.	1
JR-70-0005	<	Light, in Circuit Board Area, for Electrical Troubleshooting - with integral switch; wired constant hot.	1
		SUCTION PUMPS:	1
LP-10-2000		Suction Pump, Upgrade	1
		INSULATION:	1
LU-10-3001	< >	Insulation, Severe Weather Package one inch block foam in modular walls and roof covered with reflective insulation. Under Floor to be Spray Foam insulated after the production assembly process is complete by 24/7. All edges of reflective insulation on walls and ceiling must be taped, std.	1
		OVERHEAD GRABRAIL:	1
N0-10-9000		Grabrail, Overhead, 117 In, Stainless, Handicap Style, ILOS	1
N0-11-0503	<	Handrails,(3),Custom "L" Shape,1" SS, Entry Drs,Std Model Stainless Steel Grab Handles ILOS	1
N0-11-1500	< >	Grabhandle, 1" X 13.5", Aluminum, (1), On Exterior, IATS left side of c/s entry door, painted red FLNA 30012	1
		O2 CYLINDER RACKS:	1
NA-10-2500	>	Rack, Cylinder, Ziamatic, "M", QRM-2	1

PART NO	S	DESCRIPTION	QTY
O2 SYSTEMS COMPLETE:			1
NF-50-1001	< >	O2 Sys,LF,(2)O2/(1)Vac Port A/A,(1)O2 C/S, Std Model only Ohio style (2) oxygen outlets in action area (1) vacuum port in action area (1) oxygen outlet curbside wall at head of squad bench	1
O2 SYSTEM PARTS:			1
P0-59-7500		Regulator, Oxygen Cylinder, Preset 50PSI, Installed	1
SUCTION CONTAINERS:			1
PA-10-7001	>	Regulator/Holder, SSCOR 22000, Std Model only	1
COT MOUNTS:			1
PF-26-3580	<	Cot Mount, Stryker 6392 Performance Load with Floor Plate includes constant hot power supply for battery charging Eng note set up same as 369078	1
IV HOOKS:			1
PP-20-1000	< >	IV Hook, Perko, (1), W/Straps, STD curbside and streetside standard locations	2
PU-10-1000		Kickplate, 8" Brushed S/S, Face Of Squad Bench	1
PU-10-2000		Kickplate, 8" Brushed S/S, On Face of Basewall	1
MISC. INSTALLED HARDWARE/EQUIPMENT:			1
R5-10-3000	< >	Bracket, SCBA Pack, Un-5-30-2-Sf See ref drawings (1) Compt "B" wall 2 near wall 1 (1) Compt "E" wall 2 near wall 1	2
R5-11-5700	<	Seatbelt, Assy, (6) Point, (1) EA - Change Notice 8 -Compliant (1) for CPR side seat (if Required) (2) for squad bench (Standard)	3
DRI-DECK/TURTLETILE:			1
RA-10-1000	>	Dri Deck, Red, All Compt. Floors and Shelves	1
HOLDER, CYLINDER:			1
RF-11-5000	< >	Holder, Cylinder, Single, Ferno #521, Installed -CN 10 Certified Wall 3 of compt "B" set up for D cylinders	2
STRAPS, INSTALLED:			1
RK-13-3500	<	Seat Belt, Across Compt Opening Install a strap in compt "A" forward area for backboard storage	1
MODULE INTERIOR			1
RU-05-0000		Interior Cabinets - Duralite Construction, Wood -CN 10 Compliant	1
MICA COLOR:			1
RU-14-1900		Mica,Dove Gray Over Pewter Brush	1
SUB FLOORING:			1
RZ-99-0025		Flooring, Wood, Type 3/7/9, Std	1
FLOORING:			1
T0-11-8201	XU <	Flooring, Lonplate II, Black, #443TX ILOS (SAP# 10168306) Ref SO-FL-351219	1
SEAMLESS ATTENDANT SEATS:			1
T5-10-0001	XU <	SEAT, CHILD, ASH GRAY #1880 S ILOS (SO-SEAT-369078)	1

PART NO	S	DESCRIPTION	QTY
		SEAT,CHILD, ASH GRAY, #1880S swivel base	
		SEAMLESS UPHOLSTERY:	1
T5-25-0300		Upholstery, Seamless, Ash Gray, ILOS	1
		BULKHEAD CABINET:	1
TF-50-1200	<	Cabinet, BH, FrtlNr, Non-WT, EMS- F/R MAV, W/72"HR Per engineer design pass thru	1
		O2 DOOR:	1
TK-10-5000	>	Lexan Flap W/Hinge	1
		GLOVE HOLDERS:	1
TN-20-1001		Cabinet, Glove Box Holder,(3),Above C/S door, Std Model only	1
		RIGHT FRONT CABINET:	1
TU-19-SR10	XS < >	Cabinet, RF, Combo, EMS MAV, Custom (SO-RF-369078) RF cabinet to have Inside/Outside access to "A" Compartment See ref drawings	1
		RF CABINET DOORS W/PUREAIR A/C	1
TU-20-9000	<	Door, Dual Wood, Right Front Cabinet See ref drawings	1
		LEFT FRONT CABINET:	1
TU-50-2000	< >	Cabinet, Left Front, EMS F/R,MAV, W/67" H.R. Full height cabt behind attendant's seat for circuit board. No cabt "S".	1
		HARDWARE,LATCHES AND LOCKS:	1
		HARDWARE,LATCHES AND LOCKS:	1
V0-10-0500	< >	Handle, C, Pull, Installed,(1) Ea,STD (2) RF Cabinet doors (1) CSR cabinet door (1) Bio waste drawer in squad bench (2) Added CO for cabt J ISOS opening	4
V0-10-0500	< >	Handle, C, Pull, Installed,(1) Ea,STD -RF Cabinet(s)	2
V0-10-2000	< >	Latch, Plunger Roller, Installed (4) RF cabinet doors (2) CSR cabinet door (2) Added CO cabt J doors, bottom of doors	6
V0-10-2000	< >	Latch, Plunger Roller, Installed -RF Cabinet(s)	2
V0-11-5000	< >	Latch, Lever, No Key, Installed -CN10 Certified- Rated 5lb. (2) Top of RF cabinet doors (1) CSR cabinet (2) Top of cabt J doors	5
V0-14-1001	>	Latch, Lever, W/Key, Installed, "L" Cabt Wood Door	1
		SQUAD BENCH:	1
V5-20-14SR	XS < >	Squad Bench, Custom (SO-SB-369078) SR #2181977F	1

PART NO	S	DESCRIPTION	QTY
		slide out bio waste drawer at head of squad bench, slide out towards step well	
		Sharps/waste at head of squad bench to have access flaps on top of bench	
		LID 170 INCH BOX:	1
V5-64-1501	<	Lid, Squad Bench, Single W/Bio-Waste, 170", Std Model only Sharps/waste at head of squad bench to have access flaps on top of bench	1
		HARDWARE:	1
V5-80-1005		Handle, Trimark, Squad Bench, STD	1
V5-82-2500		Strut, Gas, 60 LB, Installed, ILOS, Mods	1
		CURBSIDE SPLINT CABINET 160-170 inch Module	1
VA-40-2950		Curbside Splint Cabt, None	1
		CURBSIDE REAR CABINET:	1
VF-20-5400	< >	Cabinet, C/S Rear, 170 F/R MAV, W/72" H.R. (SO-RR-369078)	1
		Wood door hinged on right.	
		CABINET H, BASEWALL, 170", T9	1
VH-H4-0400		H, Cabinet, Deleted	1
		CABINET I, BASEWALL 170", T9	1
VH-I4-0400		I, Cabinet, Deleted	1
		CABINET M, BASEWALL 160" & 170", T1/T9	1
VH-M2-0300		M, Cabinet, deleted	1
		CABINET O, BASEWALL 160" & 170", T9	1
VH-O2-0100		O, Cabinet, full height, std	1
		CABINET CPR, BASEWALL, 160" & 170", T9	1
VH-Q1-0100		CPR, side seat, std	1
VH-Q1-0350		CPR, side seat, flip up lid, Standard Model Only	1
		CABINET J, STREETSIDE UPPER 170", T9	1
VI-J4-SR00	XS < >	J, Cabinet, Custom (SAP#) See marked up ref drawing's SR2181977F	1
		"H/J" cabinet with inside/outside access and two wood doors that match material of squad bench rear cabinet.	
		CABINET K, STREETSIDE UPPER 160" & 170", T9	1
VI-K3-0110		K, Cabinet, std, with full height "D"	1
		CABINET L, STREETSIDE UPPER 160" & 170", T9	1
VI-L2-SR00	XU < >	L, Cabinets, Custom (SO-L-369078) see reference drawings SR2181977F L1 one large cabinet with lexan sliders L2 will be a locking wood door approx. 18"H x 14.75"W x 17.75"D	1
		BASEWALL DOORS:	1
VK-16-5000		Cab O, Gray Lexan Slider -NOT CN 10 Compliant	1
		TELEMETRY AREA WORK SURFACE	1
VP-10-5461		Telemetry Tray, Poured, Gray	1
		ACTION AREA WORK SURFACE	1
VP-10-59SR	XU <	A/A Tray, W/Bio, Poured, Gray, Narrow, 50" Aisle, Extended (SO-TRAY-369078) Ref SR# - 2181977F	1
		Hand cut holes for bio waste	

PART NO	S	DESCRIPTION	QTY
		May require buildup at one end.	
		ACTION AREA CABINET:	1
VP-15-9600	<	Cabinet, A/A, EMS MAV, W/BioWaste (poured A/A tray will not fit in MAV unless wood buildup is added at forward end)	1
		with rounded corner package	
VU-14-4000	< >	Shelf, Interior, Adj, in Cabinet: (3) K, L1, O (2) CSR cabinet	5
VU-14-4001	< >	Shelf Track, Cabt, #HA24663, Upgrade, Std Model only ("C" channel/exterior shelf style track)	4
VU-15-1500	S <	Cab "J", Double Wood doors Add 1 set of double wood doors	1
VU-15-4000		Cab "K" Gray Lexan Slider -NOT CN 10 Compliant	1
VU-15-8000	>	Cab "L1" Gray Lexan Slider -NOT CN 10 Compliant	1
VU-16-4100	<	Cab "L2" Wood Door see ref drawings hinged on right.	1
		SHIP LOOSE ITEMS:	1
YY-00-SR01	XU <	Stryker Performance Pro 6086 SR - 220124F 1 Dual Wheel Lock 6086602010 4 1 Dual Cot Retaining Posts 6085034000 5 1 6086 PERFORMANCE-LOAD OPTION 6086034001 6 1 Equipment Hook 6500147000 7 1 Performance Pro Std Components 6086026000 8 1 Siderail Option 6086058000 9 1 X-RESTRAINT PACKAGE 6500001430 10 1 Trendelenburg 6085031000 11 1 Fowler O2 Bottle Holder 6500241000 12 1 Short Hook 6060036017 13 1 DOM SHIP (NOT HI, AK, PR, GM) 0054030000 14 1 No Runner/HE O2 0054200994 15 1 G-Rated Mattress 6506034000 16 1 No HE Section O2 Bottle 6506036000 17 1 LT Handel Release - Standard 6086029000 18 1 1 year parts, labor & travel 7777881660 19 1 Domestic Manual 6086600000 20 1 3 Yr X-Frame Warranty 7777881673 21 1 2 Stage IV Pole PR Option 6500310000	1
YY-10-6400		Ship Loose, W.C. Standard Items	1
YY-13-2000	<	Fire Extinguisher. (1) 5 LB. ABC, IATS, Ship Loose Installed in Cmpnt "E", wall #3	2
		WARRANTIES	1
ZZ-10-0101		Warranty, Conversion, 12 Month	1
ZZ-10-0201		Warranty, Paint, 60 month Prorated, Standard	1
ZZ-10-0300		Warranty, Structural, 15 Years, Std., Mods	1
ZZ-10-0601		Warranty, Limited Electrical	1
ZZ-10-0701		Warranty, Cabinet Construction	1

